






PRODUCT NO
SEE TABLE

REV	DESCRIPTION	REV'D BY	DATE
M	ECR S40312	BS LOW	30DEC94
N	ECR S80123	BS LOW	19MAY98
P	ECR S80251	BS LOW	17NOV98




CUSTOMER COPY

GEN. TOLERANCES		DO NOT SCALE DWG.		
X.X±0.3/XX±.01 X.XX±0.13/XXX±.005 X.XXX±0.051/XXXX±.0020 ANGLES = ±2°				
		 		
	NAME	DATE	DESCRIPTION LOW PROFILE VCC SMT 2,3 BOTTOM ENTRY ASSY WITH 0.30/0.12 LOCATING FEATURES	
DRAWN	BS LOW	17NOV98		
CHECKED		17NOV98		
APPROVED		17NOV98		
			PRODUCT NO.	92084
			SCALE	SHT 1 OF 2

PRODUCT NO	POSITIONS	DIM. A	DIM. B
92084-X04	2 X 2	2,00/.079	3,92/.154
-X06	2 X 3	4,00/.158	5,92/.233
-X08	2 X 4	6,00/.236	7,92/.312
-X10	2 X 5	8,00/.315	9,92/.391
-X12	2 X 6	10,00/.394	11,92/.469
-X14	2 X 7	12,00/.472	13,92/.548
-X16	2 X 8	14,00/.551	15,92/.627
-X18	2 X 9	16,00/.630	17,92/.706
-X20	2 X 10	18,00/.709	19,92/.784
-X22	2 X 11	20,00/.787	21,92/.863
-X24	2 X 12	22,00/.866	23,92/.942
-X26	2 X 13	24,00/.945	25,92/1,020
-X28	2 X 14	26,00/1,024	27,92/1,099
-X30	2 X 15	28,00/1,102	29,92/1,178

PLATING OPTIONS		REV
1	= 0,76um/30u" Au CONTACT AREA, SnPb SOLDER TAIL	M
3	= 0,38um/15u" Au CONTACT AREA, SnPb SOLDER TAIL	N
5	= 0,38um/15u" PdNi WITH 0,076um/3u" Au FLASH (POST PLATED)	P
6	= 0,76um/30u" PdNi WITH 0,076um/3u" Au FLASH (POST PLATED)	




RECOMMENDED PAD LAYOUT

NOTES :


- 1 HOUSING MAT'L : HIGH TEMP PLASTIC (PCT BLACK).
- 2 TERMINAL MAT'L : BeCu.
- 3 -
- 4 TERMINAL RETENTION 0,5 Kg/1,1 Lbs.
- 5 'V' CUT OPTIONAL - MANUFACTURING PROCESS OPTION.
- 6 PRODUCT DESCRIPTION CODE :

XXXXX-X XX

TOTAL POSITIONS
PLATING
BASE NUMBER



PICK-UP CAP



2,65 (REF.)
.104

7 PACKAGING :

- (a) XXXXX-XXX --- STD PACKAGING IN TUBE.
- (b) XXXXX-XXXTR --- TAPE AND REEL (CONDUCTIVE) PACKAGING WITH PICK-UP CAP (SEE FIG 1).
- (c) XXXXX-XXXTRN --- TAPE AND REEL (CONDUCTIVE) PACKAGING WITHOUT PICK-UP CAP.
- (d) XXXXX-XXXCR --- TAPE AND REEL (NON-CONDUCTIVE) PACKAGING WITH PICK-UP CAP (SEE FIG 1).
- (e) XXXXX-XXXCRN --- TAPE AND REEL (NON-CONDUCTIVE) PACKAGING WITHOUT PICK-UP CAP.

FIG. 1

NOTE 7(b) & (d)

CUSTOMER COPY

GEN. TOLERANCES		DO NOT SCALE DWG.		BERG ELECTRONICS
X,X±0,3/XX±,01		MM	INCH	
X,XX±0,13/XXX±,005				DESCRIPTION LOW PROFILE VCC SMT 2,3 BOTTOM ENTRY ASSY WITH 0,30/.012 LOCATING FEATURES
X,XXX±0,051/XXX±,0020				
ANGLES = ±2°				PRODUCT NO. 92084 SCALE SHT 2 OF 2
	NAME	DATE		
DRAWN	BS LOW	17NOV98		
CHECKED				
APPROVED				