



DESCRIPTION: M8 MALE - CABLE MOUNT - SOLDER CUP - 4 POS.



NOTE:

MATERIAL

HOUSING:
CONTACT:
NUT:
SHELL:
O-RING:

PBT UL94V-0, BLACK
COPPER ALLOY
COPPER ALLOY
COPPER ALLOY
NBR, BLACK

FINISH

CONTACT:

GOLD PLATED
OVER 50µ" NICKEL
NICKEL PLATED 60-100µ" OVER ALL
NICKEL PLATED 60-100µ" OVER ALL

ELECTRICAL




RATED CURRENT:
RATED VOLTAGE:
INSULATION RESISTANCE:
CONTACT RESISTANCE:
WATER PROOF:

5A
125V
100 mΩhms MIN.
10 MΩhms MAX.
IP67

ENVIRONMENT

OPERATION TEMPERATURE:
WIRE GAUGE:

-40°C TO +85°C
24-28 AWG



854-004-103RLSY

1 = GOLD FLASH
4 = 10µ" GOLD

RoHS COMPLIANT

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
M. SIGMON
CHECKED:

DATE:
03-04-16
DATE:

NorComp

SCALE:
N.T.S.

SHEET **1** OF **1**

REV **1**

DWG NO.

854-004-103RLSY