

Home Cubitron II Abrasives

Products | Technology | Resources | Testimonials

[United States](#) > [Products & Services](#) > [Manufacturing and Industry](#) > [Cubitron II](#) > [Products](#) > [Cable/Wire](#) > [3M™ Round, Jacketed, Flat Cable, 3759 Series, 3759/40, 100 ft.](#)

3M™ Round, Jacketed, Flat Cable, 3759 Series, 3759/40, 100 ft.

UPC# 00051138421403 3M Product Number 3759/40 3M ID 80610803043

 Print Share

.050" 28 AWG Stranded, Mass-Term, PVC/PVC, 100 ft.

- Round construction permits easier routing
- 28 AWG wire on .050 inch centers permits mass termination to broad line of IDC connectors
- Continuous bond and continuous split/bond allows for mass termination of IDC connectors
- Available in continuous bond (non-split) wire for ease of cable fabrication
- Meets external wiring requirements of National Electrical Code, Article 725 (CL2)
- Primary cable is zippable for branching or discrete terminations
- UL listed for USA and Canadian markets
- RoHS compliant

Need Help?

Questions? We can help
[Contact Us](#)

www.facebook.com
is not loading.

[Overview](#) [Support](#)

Specifications

Color

Black

Shape

Round

People who viewed this item also viewed



3M™ 4-Wall Header, .100 in.,
High Temp Option, Straight,
30 Contacts, 3440-6302



3M™ Round Conductor Flat
Cable, 3801 Series,
C3801/14, 100 ft.



3M™ Round Conductor Flat
Cable, 3365 Series, 3365/10,
100 ft.



3M™ Round Conductor Flat
Cable, 3365 Series, 3365/25,
100 ft.



3M™ High Flex Life Cable,
3319 Series, 3319/14, 100 ft.