





Crimphousing 1,25 mm		Series	425
		pitch	1,25
		Rated current1,0 A	
		Rated voltage100 VRMS / VDC	
		Withstand voltage500 VRMS for 1 minute	
		Material contactCopper alloy	
		Material insulatorThermoplast UL94V-0	
Operating temperature-40°C to +105°C			
All dimensions in mm.		max. pincount	015
Variation	Contact	Series	606
	1		
	AWG 28 - 32		
	Plating: T = Sn		
	Packaging: R = Reel		
	606-1-TX-XR		
	Crimp Tool 454		
			
	454-1-01		
	Variation		
	No. of contacts		
	Order code:		
	425-1-??-X-KS0		