



Dimensions: mm (In.)

SPECIFICATIONS	
Rating:	15A 250VAC
Insulation Resistance:	500VDC 100M $\Omega$ min.
Dielectric Strength:	1500VAC, 1 minute
Operating Temperature:	-20° ~ 65°C
Contact Resistance:	50m $\Omega$ max.
Fuse Size:	ø6.4 x 30mm/ø6.35 x 31.8mm
Housing:	PBT
Contacts:	Brass Tin Plate
Panel Thickness:	0.7 ~ 4.0mm

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eagle Plastic Devices:

[441-R39A](#) [441-R39B](#)