






FCIconnect.com

Copyright FCI


PRODUCT NUMBER
SEE SHEET 2




mat'l. code NOTE 3				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HPC
ltr	ecp	no	dr	date	tolerances unless otherwise specified	scale 1:1	title
A	V12795	RDS	10/24/91		angles linear .XX±.01/.3		VERTICAL SHROUD
B	V20224	MRC	3/3/92		linear .XXX±.005/.13		4 ROW W/1 GUIDE PIN
C	V41077	GAH	7/6/94	0'±2'	linear .XXX±.0020/.05		dwg no
D	V94441	JWS	12/30/99	dr	D.SHEAFFER 8/7/91		sheet 1 of 2 size
E	M06-0260	MHT	7/07/06	enr	S.CLARK 10/24/91		50438 A3
				chr	S.CLARK 10/24/91		type
				appd	S.CLARK 10/24/91		Product Customer Drawing
sheet index	revision	E	E				
	sheet	1	2				

form: A3


PRODUCT NUMBER	DIM.	LENGTH FORMULAS
50438-XXXX	DIM A	.100/2.54 x NO. OF COLUMNS + 1.05/26.7
	DIM B	.100/2.54 x NO. OF COLUMNS + .750/19.05
	DIM C	.100/2.54 x NO. OF COLUMNS DIVIDED BY 2 - .100/2.54



SECTION U-U



SECTION W-W



SECTION X-X

NOTES:

- PRODUCT NUMBERING CODE:

50438-X	YYY	X	
			ALWAYS "X"
			NO. OF POSITIONS (NOTE 2)
			ALWAYS "X"
			BASE NUMBER
- THIS PRODUCT IS CONFIGURED IN SIZES OF 20 THRU 122 COLUMNS IN INCREMENTS OF TWO.
i.e.: 20, 22, 24, 26,.....120, 122.
- MATERIAL: GLASS AND MINERAL FILLED THERMOPLASTIC. FLAME RETARDANT PER UL94 V-0. COLOR: BLACK.
- MANUFACTURE'S NAME, P/N, AND LOT CODE TO APPEAR ON THIS SURFACE.
- FOR DOCUMENTATION MENU, SEE SPECIFICATION BUS-01-057.

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 1st angle	product family HPC
ltr	ecn no	dr	date	tolerances unless otherwise specified		INCH/MM scale 1:1	title VERTICAL SHROUD 4 ROW W/1 GUIDE PIN
E				angles	linear .XX±.01/.3		
				0'±2'	.xxx±.005/.13 .xxx±.0020/.05		
		dr	D.SHEAFFER	8/7/91		FCJ	dwg no
		enr	S.CLARK	10/24/91			sheet 2 of 2 size
		chr	S.CLARK	10/24/91			50438 A3
		appd	S.CLARK	10/24/91			type Product Customer Drawing
sheet index	revision sheet						