


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 3230: UPDATE DWG FORMAT	3/18/08	D.GRIFFIN



PART #	LENGTH
	FEET [METER]
CC58C-05	0.5 [.15]
CC58C-1	1.0 [.30]
CC58C-1.5	1.5 [.46]
CC58C-2	2.0 [.61]
CC58C-2.5	2.5 [.76]
CC58C-3	3.0 [.91]
CC58C-4	4.0 [1.22]
CC58C-5	5.0 [1.52]
CC58C-6	6.0 [1.83]
CC58C-7.5	7.5 [2.29]
CC58C-10	10.0 [3.05]
CC58C-12	12.0 [3.66]
CC58C-15	15.0 [4.57]
CC58C-25	25.0 [7.62]
CC58C-50	50.0 [15.24]
CC58C-75	75.0 [22.86]
CC58C-100	100.0 [30.48]
CC58C-150	150.0 [45.72]
CC58C-200	200.0 [60.96]

NOTES:
INDIVIDUALLY PACKAGE IN A POLYBAG
CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2[51] / -0 >60 [1524] ≤120 [3048] = +4 / -0 >120 [3048] ≤300 [7620] = +6 / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .3 .XX = .15 PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY MCCORMICK	05/03/01		
	CHECKED BY D.PARHAM	06/06/01	CATEGORY COAXIAL	
	APPROVED BY R.CARRICK	06/11/01	PRODUCT DESCRIPTION BNC PLUG TO BNC PLUG; RG58C	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321	DWG. NO. CC58C
COLOR VARIATIONS MAY OCCUR		SCALE: NONE	CAD FILE: CC58C.SLDDRW	REV. E
		SHEET 1 OF 1		