









TERMINATED VIEW



- 1 MOLDED PARTS: UL RATED 94V-0 THERMOPLASTIC, BLACK.
- 2 CONTACTS: PHOSPHOR BRONZE PER QQ-B-750.
- 3 CONTACTS: PLATED WITH .000030 MIN GOLD IN LOCALIZED GOLD PLATE AREA, .000050 MIN TIN ON TERMINATION END, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.  
OR  
GOLD FLASH OVER PALLADIUM-NICKEL PLATE .000030 MIN TOTAL IN LOCALIZED GOLD PLATE AREA, .000050 MIN TIN ON TERMINATION END, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
- 4 POLARIZING FEATURE DOES NOT EXIST ON END OPPOSITE THE POSN #1 INDICATOR ON 10 POSN PRODUCT.



DETAIL Z  
SCALE 10:1  
TYPICAL



|       |       |       |    |            |             |
|-------|-------|-------|----|------------|-------------|
| 2.100 | 2.380 | 2.150 | 43 | 44         | 1-1658624-3 |
| 3.100 | 3.380 | 3.150 | 63 | 64         | 1-1658624-2 |
| 2.400 | 2.680 | 2.450 | 49 | 50         | 1-1658624-0 |
| 1.900 | 2.180 | 1.950 | 39 | 40         | 1658624-9   |
| 1.600 | 1.880 | 1.650 | 33 | 34         | 1658624-8   |
| 1.400 | 1.680 | 1.450 | 29 | 30         | 1658624-7   |
| 1.200 | 1.480 | 1.250 | 25 | 26         | 1658624-6   |
| 1.100 | 1.380 | 1.150 | 23 | 24         | 1658624-5   |
| .900  | 1.180 | .950  | 19 | 20         | 1658624-4   |
| .700  | .980  | .750  | 15 | 16         | 1658624-3   |
| .600  | .880  | .650  | 13 | 14         | 1658624-2   |
| .400  | .680  | .450  | 9  | 10         | 1658624-1   |
| D     | C     | B     | A  | NO OF POSN | PART NUMBER |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

|        |   |      |
|--------|---|------|
| 0 PLC  | ± | -    |
| 1 PLC  | ± | -    |
| 2 PLC  | ± | -    |
| 3 PLC  | ± | .005 |
| 4 PLC  | ± | -    |
| ANGLES | ± | -    |

FINISH

SEE NOTES

DWN  
R. SAMICK  
CHK  
C. ROHDE  
APVD  
M. WALMSLEY

25AUG03  
25AUG03  
25AUG03

PRODUCT SPEC  
108-40000  
APPLICATION SPEC  
114-40005  
WEIGHT  
-

CUSTOMER DRAWING

TE Connectivity

RECEPTACLE ASSY,  
DUAL BAR POLARIZATION,  
LEAD FREE, AMP-LATCH™ NOVO

SIZE  
A2

CAGE CODE  
00779

DRAWING NO  
C=1658624

RESTRICTED TO  
-

SCALE  
4:1

SHEET  
1 of 1

REV  
C1