



A fully screened robust range of DIN connectors for use in instrumentation and audio applications. Available in two finishes; bright nickel and non-reflective electrically conductive matt black. Robust construction incorporating cable grip and strain relief. This line socket mates with all standard and lockable plugs.

Manufactured to DIN 41 524, 45322, 45326, 45327 and 45329.

Dimensions



|                         |                                   |
|-------------------------|-----------------------------------|
| <b>Materials</b>        |                                   |
| Housing                 | Zinc Alloy<br>Heavy Nickel Plated |
| Moulding                | Nylon                             |
| Contacts                | Brass Silver Plated               |
| Cable Clamp             | Mild steel Zinc Plated            |
| Grommet                 | Black P,V,C                       |
| <b>Electrical</b>       |                                   |
| Rated Voltage           | 34 V a.c. or d.c.                 |
| Current Rating          | 2.A                               |
| Test Voltage            | 500 V r.m.s.                      |
| Insulation Resistance   | 103 MΩ min at 100 V d.c           |
| Contact Resistance      | 10 mΩ max                         |
| Capacitance (mated)     | 3pF                               |
| <b>Climatic</b>         |                                   |
| Climatic category       | 25/070/21                         |
| Temperature Range       | -25°C to +70°C                    |
| Damp heat, steady state | 21 days                           |

| Type       | Deltron No |
|------------|------------|
| 3 Way      | 600-0300   |
| 4 Way      | 600-0400   |
| 5 Way 45°  | 600-0500   |
| 5 Way 60°  | 600-0510   |
| 5 Way Dice | 600-0520   |
| 6 Way      | 600-0600   |
| 7 Way      | 600-0700   |

RoHS  
2002/95/EC  
Compliant