



AGF 20


Industrial Connectors: Measuring and Testing Equipment: Alligator clips: 4 mm system

Product description

Description Nickel-plated steel alligator clip. The special shape allows clamping of both extremely fine and thick wires. Maximum bolt diameter 10 mm. 4 mm diameter socket connection and solder connection possible.

Type	AGF 20
Order No.	930 120-000
System	4 mm system
Clamping range	10 mm
Housing Color	metal color

Drawing



Technical data

Type of contact	socket
Type of termination	4 mm socket, solder
Rated voltage	DC 60 V
Contact resistance	15 mOhm

Material

Contact material	steel
Contact surface material	nickel-plated
Housing material	steel

Environmental conditions

Temperature range	-25 °C to +100 °C
-------------------	-------------------

Inflammability class

Housing	94 HB
---------	-------