







REV.	DATE	DESCRIPTION
A	05/10/04	UPDATE DRAWING FORMAT
B	07/31/07	REVISE PART ORIENTATION



NOTE:

1. MAX. PANEL THICKNESS 2.4mm [.094]

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS		DATE		Amphenol Connex					
8						DRAWN	G.R.S.	07/31/07							
7	HEX NUT	BRASS	GOLD	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm	CHECKED				PART DESCRIPTION					
6	LOCK WASHER	BRASS	GOLD	1		ISSUED				SMA R/A BULKHEAD P.C. MOUNT JACK					
5	CONTACT PIN	BRASS	GOLD	1		SHEET		1 OF 1							
4	INSULATOR	TEFLON	NATURAL	1											
3	CONTACT PIN	BER. COPPER	GOLD	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	CAD FILE		C:/132/132203.DWG		DWG. NO. 132203.DWG					
2	INSULATOR	TEFLON	NATURAL	1						REV. B		SIZE A		SCALE NA	
1	HOUSING/BODY	BRASS	GOLD	1		DO NOT SCALE DRAWING									
DESCRIPTION					MATERIAL	FINISH	QTY								