



RBK HSS JOBBER DRILL 8.20MM – Part Number A0018.2

DIN 338/BS 328	
Flute Geometry Standard Helix, right hand spiral	
Surface finish Blue	
Point geometry Up to 2.9mm - 118° 3.0mm and above - 135° split point	
Angle, drill point	118 °
Diameter, External	8.20 mm
Length, effective	75 mm
Length, overall	117 mm
Material	HSS
RoHS Compliant	NA