


Dimensions: mm (In)



Electrical Specifications:

- Rating: 5A/125VAC, 3A/250VAC
- Insulation Resistance: 500VDC 100M Ω min.
- Dielectric Strength: 1500VAC for 1 minute.
- Contact Resistance: 1A/2.5VDC 50m Ω max.

Mechanical Specifications:

- Circuit: 2P SPST On-Off

Mouser Stock No.	Color	Absolute Maximum Rating (Ta=25°C)							Electro-Optical Cha. (IF=20mA, Ta=25°C)				
		P (mW)	IF (mA)	IFM (mA)	VR (V)	Top. (°C)	Tatg (°C)	VF (typ.)	IR (max)	Cd(mcd) Min	Cd(mcd) Typ.	λ P(typ) (nm)	$\Delta\lambda$ (typ) (nm)
107-DS850K-0R	Red	80		300		-30~	-30~	1.7V	100 μ A	12	24	660	30
107-DS850K-0G	Green	100	40	100	4	+85	+100	2.1V	100 μ A	10	15	570	30
107-DS850K-0Y	Yellow	100		100				2.1V	100 μ A	2	4	555	30

Rocker Switches

107-DS850K-0R, 107-DS850K-0G, 107-DS850K-0Y

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

[107-DS850K-0G](#) [107-DS850K-0R](#) [107-DS850K-0Y](#)