


HOME THEATRE AUDIO & VIDEO CABLES


No. 70-1100




MEDIA STAR™ AUDIO/MULTIMEDIA CABLE

LKG MediaStar™ cables employ better materials throughout. Pure copper conductors receive a refined tin plating to prevent chemical degradation which commonly begins to occur to raw copper within months of manufacture. This plating assures true fidelity without losses in the mid and high audio ranges; for years. The inner cable is heavier than most (26ga. vs 28ga.) to reduce electrical resistance; shielding has also been increased. The outer PVC insulation is advanced (SRPVC) material that will increase life and durability by years. And the light grey color blends practically unnoticed into your home or office. Bulk MediaStar™ Cable is ideal for custom audio connections. Available in 100 ft. and 300 ft. spools.

No. 70-2100



No. 70-3100



Single Conductor with Shield:

No. 70-1100 - 100 ft. Spool

No. 70-1300 - 300 ft. Spool

Two Conductor with Shield:

No. 70-2100 - 100 ft. Spool

No. 70-2300 - 300 ft. Spool

Dual Shielded Conductors:

No. 70-3100 - 100 ft. Spool

No. 70-3300 - 300 ft. Spool

S-Video or S-VHS CABLES

For use with S-VHS equipment or television sets that use an S-connector for separate luminance and chroma signals. The Philmore cables use gold plated (4-pin mini-din) connectors throughout for life-long dependable service. S-Cable is available in bulk. See S-Video or S-VHS CABLES below.



LOW LOSS S-VHS CABLES WITH GOLD CONNECTORS

A heavily shielded, strong and durable S-VHS cable that is possibly the best available. Multiple strands of synthetic fibers reinforced for strength, a heavy rubber insulation jacket. Connectors Gold plated, standard S-VHS four pin type. A 95% copper braid shield coverage is effectively 100% shielding in electrical terms, low loss. Available in preassembled S-VHS cables and bulk as well.


Bulk cable user information: Cable is comprised of two fully shielded (1 red and 1 yellow) 75 ohm coaxial cable. Coaxial cable outside diameter .122", inner insulator is PE foam .087 O.D. (24 awg stranded center conductor) with a nominal capacitance of 16.9 picofarads per foot. Shield is copper braid woven for 95% coverage. Total cable O.D. is .315" outer insulation dark grey in color.

No.	Size	Description
VHS41	1 ft.	4-pin male on each end
VHS43	3 ft.	4-pin male on each end
VHS46	6 ft.	4-pin male on each end
VHS412	12 ft.	4-pin male on each end
VHS406	6 ft.	4-pin male to female
VHS4012	12 ft.	4-pin male to female
VHS425	25 ft.	4-pin male to male
VHS450	50 ft.	4-pin male to male
VHS410	100 ft.	4-pin male to male

No. VHS4 - S-VHS In-Line Adaptor
(4 Pin Mini Din Female)



S-Video or S-VHS CABLES



Bulk "S-Video" cable for making your own cables in whatever lengths needed. Use with Philmore connectors Nos. EMA4 and 45-106G etc.. The cable has a black PVC outer insulation, red and white inner conductors (two) that have insulated shields for a total of four conductors. Supplied on spools.

No.	size
45-525	250 feet
45-550	500 feet
45-510	1,000 feet

Recommended Philmore S-VHS Male Connectors

NO. ETA4 - 4 Pin Mini DIN, Plastic handle

NO. 45-106G - 4 Pin Mini DIN, Metal handle



With Gold S-VHS connectors

No. 45-4803 - 3ft

No. 45-4806 - 6ft

No. 45-4812 - 12ft

No. 45-4825 - 25ft

Bulk Cable on Spool

No. 45-48100 - 100ft spool

No. 45-48300 - 300ft spool

Recommended Philmore S-VHS Male Connectors

NO. 45-186G - 4 Pin Mini DIN, Metal handle