



575C1 Vane and Hotwire Velocity Meter

APPLICATIONS

- Air flow measurements in heating, ventilation and air conditioning systems
- Air duct analysis
- Fume hoods
- Flue Registers
- Exhaust grills
- Hotwire velocity meter enables user to read below 80fpm applications (low flow)



Comes hardwired with protective boot (A604)

Turn over for
technical
information
and accessory
part numbers.

**The
Value
Leader™**

Features

- (Vane) Air flow 0.4 to 25 m/s (Also reads km/s, ft/min, knots/h, miles/h)
- (Hotwire) Air flow 0.2 to 20 m/s (Also reads km/s, ft/min, knots/h, miles/h)
- Temperature -5° to 175° F (-20° to 80°C)
- Data record function for maximum and minimum temperature and air velocity rearing
- Download to a computer using the RS-232 port and optional A500 cable. (The 555 uses Microsoft® Hyper Terminal to download and display air velocity and temperature on your PC.)
- 39" cable length with Lemo connector
- Data Hold
- Auto Power Off
- Protective boot and soft carrying case included



TECHNICAL SPECIFICATIONS AND ACCESSORIES

Digital

- Multimeters •
- Clamp Meters •
- Hand-held
- Oscilloscopes •
- Refrigerant &
Combustible Gas
- Leak Detectors •
- Temperature
- Testers • BNC
- Coax Cable •
- Connectors •
- Test Leads •
- Accessories

Test Products International, Inc.

Headquarters:
9615 SW Allen Blvd.
Beaverton, OR 97005
USA
503-502-9197
Fax: 503-520-1225
email:
info@tpi-thevalueleader.com

Test Products International, Ltd.

342 Bronte St. South
Unit 9
Milton, Ontario L9T
5B7
Canada
905-693-8558
Fax: 905-693-0888
email:
info@tpicanada.com

Test Products International UK Ltd.

Longley House, East Park
Crawley, West Sussex
RH10 6AP England
Tel: +44 (0)1293 561212
Fax: +44 (0)1293813465
contactus@tpieurope.com

575 Vane and Hotwire Velocity Meter

SPECIFICATIONS

Display	Dual digits LCD with function annunciation
Measurement	m/s, km/s, ft/min, knots, mile/h, °C, °F
Measurement Range and Accuracy:	
Air Flow (Vane)	0.4 ~ 25 m/s ($\pm 2\%$ of reading ± 3 digits)
(Hotwire)	0.2 ~ 20 m/s ($\pm 5\%$ of reading ± 3 digits)
Temperature	-5°F ~ 175°F ($\pm 1\%$ of reading $\pm 1.0^\circ\text{F} \pm 3$ digit)
	-20°C ~ 80°C ($\pm 1\%$ of reading $\pm 0.5^\circ\text{C} \pm 3$ digit)
Operating Temperature	0 ~ 50°C (32°F ~ 122°F)
Operating Humidity	Less than 80% R/H
Powering	1.5V AAA x 6EA
Optional Accessories	A500 RS-232 cable
	A901 soft shoulder strap carrying case

Distributed By:



To learn about the entire
line of TPI products visit:

www.tpi-thevalueleader.com

L 575C1-0105
Copyright © 2005 Test Products International, Inc.