

British Plug Top Fuse

Fast/Medium

TDC180



CATALOG SYMBOL: TDC180 (8AG)
FAST/MEDIUM BRITISH PLUG TOP FUSE
240 VOLTS AC
BS1362, IEC 269-3A

Electrical Ratings (Catalog Symbol and Amperes)

240 Volts AC


TDC180-1A	TDC180-5A	TDC180-13A
TDC180-2A	TDC180-7A	—
TDC180-3A	TDC180-10A	—

Rated Current	Rated Volt AC	Breaking Capacity	Power Dissipation Max.	Color	Approvals
1A	240 (264 max.)	6000A 264VAC, 50Hz p.f. 0.3 - 0.4	1 Watt	Black	Asta, BSI
2A				Black	
3A				Red	
5A				Black	
7A				Black	
10A				Black	
13A				Brown	

- **Type TDC180.**
- 1/4" x 1" fast/medium British plug top fuse.
- Ceramic tube - end caps: silver-plated copper.
- Packaging: x 10, x 100, x 1000.
- Weight: 2.5g.

CE CE logo denotes compliance with European Union Low Voltage Directive (50-1000 VAC, 75-1500 VDC). Refer to BIF document #8002 or contact Bussmann Application Engineering at 314-527-1270 for more information.


Dimensional Data



Limits for Pre-arcing Time

	1.0 In.	1.6 In.	1.9 In.
In	MIN	MIN	MAX
1A - 13A	1000 hours	30 min.	30 min.

Envelope



The only controlled copy of this BIF document is the electronic read-only version located on the Bussmann Network Drive. All other copies of this BIF document are by definition uncontrolled. This bulletin is intended to clearly present comprehensive product data and provide technical information that will help the end user with design applications. Bussmann reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Bussmann also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.

TDC17 (C17)



Agency Approvals: Conforms to BS646
For use in plugs and socket outlet adaptors to BS546

Dimensions (mm): 5 x 19

Breaking Capacity: 1000A at 0.6 lagging power factor - 250V

Order Code: TDC17- + Rating
Type: Fast Acting, high breaking capacity
Construction: Ceramic cartridge, silvered end caps
Ratings (A): 1, 2, 3, 5
Rated Voltage: 250V ac
Packing: 10's, 100's, 1000's

Rating (A)	Colour Code	Max. mV drop @ I_n
1	Green	500
2	Yellow	300
3	Black	235
5	Red	160

TDC180 (C180)



Agency Approvals:



The British Standard plug top fuse carries ASTA accreditation for 2 to 13A, all fuses comply with BS1362 and carry the BSI Kite Mark.

Dimensions (mm): 6.4 x 25.4

Breaking Capacity: 6000A/250V @ 0.3 - 0.4 p.f.

Order Code: TDC180 + Rating or C180 + Rating
Type: Fast Acting
Construction: Ceramic cartridge, silvered end caps
Ratings (A): 1, 2, 3, 5, 7, 10, 13
Rated Voltage: 240V ac
Packing: 10's, 100's and 1000's

Rating (A)	Colour Code	Rating (A)	Colour Code
1	Black	7	Black
2	Black	10	Black
3	Red	13	Brown
5	Black		