




AD6010(T)-7 SERIES

External Dimensions



Frame:Plastic(UL:94V-0)
Impeller:Plastic(UL:94V-0)
Lead wire:UL1007AWG26

Specifications(Nominal)

*:Noise is measured at the distance of one (1) meter from the axis of intake.


Bearing type: ◎=Ball ※=Sleeve ●=Hypro bearing

Frame size (mm)	Model No.	Bearing System Type	Rated Voltage (VDC)	Current (A)	Power (W)	Rated Speed (rpm)	Maximum AirFlow (CMM)	Maximum AirFlow (CFM)	Maximum Pressure (InAq)	Maximum Pressure (mmAq)	*Noise Level (dB/A)	Weight (g)
60x60x10	AD0605DB-G70(T)	◎ ※ ●	5	0.05	0.25	2800	0.237	8.390	0.050	1.190	16.1	23.0
	AD0605LB-G70(T)	◎ ※ ●	5	0.09	0.45	3500	0.301	10.640	0.070	1.830	22.9	
	AD0605MB-G70(T)	◎ ※ ●	5	0.12	0.60	4200	0.339	12.000	0.090	2.290	28.0	
	AD0605HB-G70(T)	◎ ※ ●	5	0.22	1.10	4900	0.419	14.820	0.120	3.000	35.0	
	AD0612DB-G70(T)	◎ ※ ●	12	0.04	0.48	2800	0.237	8.390	0.050	1.190	16.1	
	AD0612LB-G70(T)	◎ ※ ●	12	0.09	1.08	3500	0.301	10.640	0.070	1.830	22.9	
	AD0612MB-G70(T)	◎ ※ ●	12	0.11	1.32	4200	0.339	12.000	0.090	2.290	28.0	
	AD0612HB-G70(T)	◎ ※ ●	12	0.12	1.44	4900	0.419	14.820	0.120	3.000	35.0	
	AD0624LB-G70(T)	◎ ※ ●	24	0.03	0.72	3500	0.301	10.640	0.070	1.830	22.9	
60x60x10	AD0624MB-G70(T)	◎ ※ ●	24	0.06	1.44	4200	0.339	12.000	0.090	2.290	28.0	23.0
	AD0624HB-G70(T)	◎ ※ ●	24	0.07	1.68	4900	0.419	14.820	0.120	3.000	35.0	

Specifications subject to change without notice.

The specification for bearing type is for reference only , for more bearing types information, please contact with your ADDA sales representative, thanks!!

(網頁上呈現產品軸承資訊均以2Ball為主, 若需其他產品資訊請聯絡您在ADDA的業務代表, 謝謝!!)



*Motor protective circuit and third lead wire functions

0	1	2	3	4	6	7	8	9	A	B
✓					✓					

*Safety approvals

UL	UL	SP	CE	CE
✓	✓		✓	✓

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADDA:](#)

[AD0612HX-G76\(T\)-LF](#) [AD0605MS-G70-LF](#)