

Between Series Adaptor 36_BMA-SMA-50-1/199_U

Description

Bulkhead adaptor plug/jack
BMA plug (male) / SMA jack (female)

Interface standards

Series BMA - IEC 60169-33_MIL-STD-348A/321

Series SMA - IEC 60169-15_MIL-STD-348A/310_CECC 22110



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz
VSWR	DC - 18 GHz ≤ 1.03 + 0.015 f (GHz)

Mechanical Data

Number of matings	500
Weight	0.0034 kg

Environmental Data

Operating temperature	-65 °C to 125 °C
2011/65/EU (RoHS)	compliant

Material Data

Interface - BMA plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PFA / PTFE	
Coupling nut	Stainless Steel	
Gasket	NR (Natural Rubber)	

Interface - SMA jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing	DCA-00014012
Mounting hole	DOU-00008972

Ordering Information

Single package	36_BMA-SMA-50-1/199_UE
----------------	------------------------

Between Series Adaptor 36_BMA-SMA-50-1/199_U