



PCSH-B-CR



- Black neoprene sleeving slips on Pan-Steel™ Stainless Steel Ties and custom length banding and is used on applications requiring improved gripping on non-resilient objects, separation between dissimilar metals, and added bundle protection. Can be used indoors or outdoors (excellent ultraviolet resistance, good resistance to petroleum, and many chemicals). Provides full separation between the ties and the material to which you are fastening.
- Operating temperature range 41°F – 200°F (5°C – 93°C)
- Supplied in 100 ft (30.5m) reels
- "C" shaped channel design available in types PCSS-B-CR and PCSH-B-CR cushion sleeve
- "U" shaped channel design available in type PCSSH-B-CR cushion sleeve

■ Part Number	PCSH-B-CR
■ RoHS Compliancy Status	Compliant
■ Part Description	Cushion sleeving used with heavy cross section ties or custom length banding system, "C" shaped channel design.
■ Color	black
■ Length (ft.)	100
■ Length (m)	30.5
■ Width (In.)	.47
■ Width (mm)	11.9
■ Pricing Description	Cushion Sleeving, Heavy, 100ft (30.5m) x .47" (11.9mm) Wd
■ Min. Order UOM	RL
■ Min. Order Qty.	1
■ BOM Qty. (# of Pkgs.)	

