









2		1					
LOC	DIST	REVISIONS					
J		P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	REVISED ECR-05-006022	1JUL05	L.Z	S.Y
			A1	REVISED PER ECO-09-024927	09NOV09	KK	AEG



50 POS (-4) ONLY



GENERAL TOLERANCE	
10 ≥	±0.2
30 ≥ > 10	±0.25
100 ≥ > 30	±0.3
ANGLES	±3°

96	47	59.69	64.06	75.7	81.7	71.49	75.7	0.00076 MIN	4-2-6
68	33	41.91	46.28	57.9	63.9	53.71	57.9		2--5
50	24	30.48	34.85	46.5	52.5	42.28	46.5		4-2-4
28	13	16.51	20.88	32.5	38.5	28.31	32.5		4-2-2
20	9	11.43	15.8	27.4	33.4	23.23	27.4	0.0002 MIN	4-2-1
96	47	59.69	64.06	75.7	81.7	71.49	75.7		--6
68	33	41.91	46.28	57.9	63.9	53.71	57.9		4--5
50	24	30.48	34.85	46.5	52.5	42.28	46.5		4--4
36	17	21.59	25.96	37.6	43.6	33.39	37.6		4--3
28	13	16.51	20.88	32.5	38.5	28.31	32.5		4--2
20	9	11.43	15.8	27.4	33.4	23.23	27.4		4-5174341-1
POS	N	A	B	C	D	E	F	GOLD THK	PART NO.

- 1 P.C BOARD HOLE LAY-OUT AS SHOWN FIG.1
- 2 USED SCREW SIZE; M2.5 PANHEAD SCREW
- 3 CONNECTOR TO BE MATED;
X-5174340-X
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
SEE ABOVE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH ± -

SEE ABOVE

DWN Roy Hao 17Aug04

CHK Steven Yao 17Aug04

APVD I.Enomoto 17Aug04

PRODUCT SPEC 108-60037-1

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

Tyco Electronics AMP K.K.
Kawasaki, Japan

NAME POST HEADER (HORIZONTAL, WITH R/L)
AMPLIMITE .050 SERIES II CONN.
TYPE B

SIZE A3 CAGE CODE 00779 DRAWING NO C-5174341

RESTRICTED TO

SCALE 2:1 SHEET 1 OF 1 REV A1