



LOC	DIST	P	ZONE	LTR	DESCRIPTION	DATE	APPD
G	14				REV, RDRW, & SM PKG PER 0720-0040-93	3-26-93	18 DAP



AMP WIRE RANGE	E13268 Listed
22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
22-16 AWG SOLID OR STRANDED	NOT APPLICABLE

1 STAMP AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPECIFICATION
MIL-T-7928, COMMERCIAL WIRE RANGE IS 22-16



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX	DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm (INCHES) TOLERANCES ON: 2 PLG DEC ± - 3 PLG DEC ± - ANGLES ± -
VOLTAGE RATING: NOT APPLICABLE	DR 3-26-93 TA BRINKMAN CHK 3-26-93 DA PATTERSON
WIRE CROSS SECTIONAL AREA RANGE: 0.26-1.65mm² (509-3,260) CIR MILS SOLID OR STRANDED	APPD 3-26-93 DE MILLER APPD 3-26-93 JL NECKLEY
FINISH TIN PLATE 0.00254 [L.000100] MIN THK PER MIL-T-10727	APPD 3-26-93 JL NECKLEY

AMP	NAME	TERMINAL, SPADE TONGUE, SOLISTRAND™
AMP Incorporated Harrisburg, PA 17105-3608	APPLICATION SPEC	SIZE CAGE CODE DRAWING NO
	WEIGHT	SCALE 10:1
		SHEET 1 OF 1

100	LOOSE PIECE, BOX	8-323127-1
---	LOOSE PIECE	323127
QUANTITY	PACKAGE TYPE	PART NO