




Model Number:	55-2950	
GENERAL SPECIFICATIONS		
Nominal Diameter:	8 inch	
Rated Lmpedance:	8 ohms	
Operating Bandwidth:	65Hz ~ 4.5KHz	
Power Handling Capacity:	100W RMS	
Sensitivity (1W/M):	94 dB	
Voice Coil Diameter:	2 inch	
THIELE-SMALL PARAMRTER		
Resonance Frequency	Fs:	65 Hz
DC Resistance	Re:	7.2 ohm
Mechanical Q Factor	Qms:	2.5
Electrical Q Factor	Qes:	0.303
Total Q Factor	Qts:	0.27
Equivalent Cas air load	Vas:	46.4 liters
Coil Inductance	Le:	1.08 mH
Efficiency Bandwidth Product	EBP	214.52
Voice Coil Over Hang	X-max	3.5mm
PHYSICAL INFORMATION		
Basket:	Stamped Steel	
Magnet Type:	30 OZ	
Cone Material:	None press paper	
Surround:	cloth	
Dust Cap:	paper	
Damper:	cloth	





ALL DIMENSIONS ARE IN MILLIMETERS