


unit:mm



NOTE:

- 1) CONDUCTOR RESISTANCE: $1\ \Omega$ Max;
INSULATION RESISTANCE: $50M\ \Omega$ Min;
HI-POT: DC 300V;
SHORT AND OPEN 100% TESTING
DIE NO.: P1 OZ07I05 P2 OZ07I01
- 2) RoHS COMPLIANT.
- 3) 1PCS/PE BAG+HEADER PAPER+LABEL(7).
- 4) 25PCS/INNER BOX+LABEL(8).
- 5) 2PCS INTO A OUTER BOX.

4	INNER JACKET PE RoHS
3	OUTER JACKET 45Pa PVC BLACK(1101) RoHS
2	SATA 7PIN CONNECTOR BLACK PBT TERMINAL PLATED GOLD 3U"
1	SATA 3.0(2C*26AWG+AL+2D)*2C OD:2.2*7.6MM RED 1000MM RoHS

PINOUT:

1	DRAIN	1	G
2	SIGNAL(WHITE)	2	DR+
3	SIGNAL(WHITE)	3	DR-
4	DRAIN	4	G
5	SIGNAL(WHITE)	5	DT-
6	SIGNAL(WHITE)	6	DT+
7	DRAIN	7	G

A	FIRST EDITION	J.2472	27/01/11
REV.	ECR	DESCRIPTION	C.N. DATE
		Rotronic Co., Ltd.	
UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETERS ANGULAR TOLERANCE: ±1.0°		ROLINE Internal SATA 6.0 Gbit/s Cable, angled, 1.0m	
DIMENSIONS	TOLERANCE	CHKD.	
0.00 TO 30.00mm	±0.10mm		
30.01 TO 80.00mm	±0.13mm	DR.	
80.01 TO 150.00mm	±0.15mm	J.2472	APPD.
150.01mm	±0.20mm	PART NO.	
MATERIAL	MATERIAL	11.03.1565	
FINISH	FINISH	SCALE	
		SHEET	1 / 1
		UNIT	MM
		SIZE	A4
		REV.	A