


PRODUCT NUMBER	DIM "A"	DIM "B"	APPLICATION
78628-001	.860 [21.84]	.300 [7.62]	E.S.D., SEE SHT. 4
78628-001LF	.860 [21.84]	.300 [7.62]	E.S.D., SEE SHT. 4
78628-002	.775 [19.68]	.380 [9.65]	MECH., SEE SHT. 2&3
78628-002LF	.775 [19.68]	.380 [9.65]	MECH., SEE SHT. 2&3




NOTES:


1. MATERIAL: AISI 416 STAINLESS STEEL.
2. THIS PRODUCT WITH AN LF SUFFIX MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
3. THIS PRODUCT IS NOT INTENDED TO BE EXPOSED TO MANUFACTURING SOLDER PROCESSES.

mat'l. code NOTE 1				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HPC
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
B	V31851	GIP		11/11/93	angles	.XX±.01/.3	END MOUNTED GUIDE PIN
C	V40690	RMP		3/29/94	linear	.xxx±.005/.13	
D	V00719	LSS		4/6/00	0'±2'	.xxx±.0020/.05	
E	V05-0974	LP		10/31/05	dr	L.SANDERS 4/6/00	dwg no 78628 sheet 1 of 4 size A3
F	M06-0260	MHT		7/07/06	enr	M.GRAY 4/6/00	
					chr	M.GRAY 4/6/00	
					appd	M.GRAY 4/6/00	type Product Customer Drawing
sheet index	revision sheet	F	1				


PRODUCT NO.
78628-002
78628-002LF



GUIDE PIN, MOUNTED TO RECPT.



GUIDE PIN FIRST CONTACT



HOUSING FULLY MATED

END MOUNTED GUIDE PIN ON RECEPTACLE (MECHANICAL)

NOTES:

- P/N 78628-002 / 78628-002LF TO BE USED IN MECHANICAL APPLICATIONS ONLY, IT CAN BE MOUNTED IN RECPT. OR HEADERS, DESIGNED TO MAKE FIRST CONTACT WHEN HOUSING FACES ARE .035" APART.


mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HPC
ltr	ecr	no	dr	date	tolerances unless otherwise specified		title
F					angles linear .XX±.01/.3		END MOUNTED GUIDE PIN
					0'±2' .XXX±.005/.13		dwg no
					.XXXX±.0020/.05		sheet 2 of 4 size
				dr	L.SANDERS 4/6/00		78628 A3
				enr	M.GRAY 4/6/00		type
				chr	M.GRAY 4/6/00		Product Customer Drawing
				appd	M.GRAY 4/6/00		
sheet index	revision sheet						

form: A3


PRODUCT NO.

78628-002


78628-002LF



GUIDE PIN, MOUNTED TO HEADER



HOUSING FULLY MATED



GUIDE PIN FIRST CONTACT

END MOUNTED GUIDE PIN ON HEADER
(MECHANICAL)

NOTES:

1. P/N 78628-002 / 78628-002LF TO BE USED IN MECHANICAL APPLICATIONS ONLY, IT CAN BE MOUNTED IN RECP. OR HEADERS, DESIGNED TO MAKE FIRST CONTACT WHEN HOUSING FACES ARE .035" APART.

mat'l. code				surface ISO 1302	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HPC
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
F					angles linear 0°±2'	scale 1:1	END MOUNTED GUIDE PIN
			dr	L.SANDERS	4/6/00		dwg no
			enr	M.GRAY	4/6/00		sheet 3 of 4
			chr	M.GRAY	4/6/00		size
			appd	M.GRAY	4/6/00		A3
sheet index	revision sheet						type Product Customer Drawing

form: A3



FCIconnect.com

Copyright FCI

PRODUCT NO.
78628-001
78628-001LF

NOTES:

1. P/N 78628-001 / 78628-001LF TO BE USED FOR ELECTRICAL DISCHARGE APPLICATIONS, MOUNTED IN HEADER ONLY. DESIGNED TO MAKE CONTACT WHEN HOUSING FACES ARE .060" APART.

mat'l. code				surface ISO 1302	tolerance ISO 406 ISO 1101	projection 	product family HPC
ltr	ecn	no	dr	date	tolerances unless otherwise specified	INCH/MM scale 1:1 	title
F					linear .XX±.01/.3		END MOUNTED
				angles	linear .xxx±.005/.13		GUIDE PIN
				0'±2'	linear .xxx±.0020/.05		
				dr	L.SANDERS 4/6/00		dwg no
				enr	M.GRAY 4/6/00		sheet 4 of 4
				chr	M.GRAY 4/6/00		size
				appd	M.GRAY 4/6/00		A3
sheet index	revision sheet						type
							Product Customer Drawing

form: A3