





D




C

B

A




Mating Part Number		
3120-ALL	3110-XX-001-11-XX	3110-XX-001-13-XX
3110-XX-002-13-XX	3110-XX-003-13-XX	



NOTES:
Insulator Material: PBT, UL 94V-0
Contact Plating: Nickel 50μ"
Contact Material: Brass

Current Rating : 1A AC,DC
Contact Resistance: 20MΩ Max.
Dielectric Withstanding: AC 500V
Insulator Resistance: 1000MΩ Min.
Operating Temp.: -40°C~+105°C

NUMBER OF POSITIONS	DIMENSION	
	A	B
06	4.0	11.2
08	6.0	13.2
10	8.0	15.2
12	10.0	17.2
14	12.0	19.2
16	14.0	21.2
18	16.0	23.2
20	18.0	25.2
22	20.0	27.2
24	22.0	29.2
26	24.0	31.2
28	26.0	33.2
30	28.0	35.2
34	32.0	39.2
36	34.0	41.2
40	38.0	45.2
44	42.0	49.2
50	48.0	55.2



UNLESS TOLERANCE		DRAW BY		
GENERAL	ANGLE	DESIGN BY		
X. ± 0.30	X.* ± 3.0°	CHECK BY		
.X ± 0.20	.X* ± 2.0°	APPROVE BY		
.XX ± 0.15	.XX* ± 1.0°	SCALE	SHEET	UNIT
.XXX ± 0.10	.XXX* ± 0.5°	1:1	1/1	MM

CnC Tech,LLC

Part NO.
3130-XX-0104-99

DRW NO: REV: A