


# SMA

## Panel Jack Receptacles – 4-hole Flange

Amphenol®

SMA



### SMA PANEL JACK RECEPTACLES – 4-hole square flange mount

| Terminal Type             | Dimensions In. (mm)                                          |               |               |            |           | Plt. | Ins. | Amphenol Number       | Fig. |
|---------------------------|--------------------------------------------------------------|---------------|---------------|------------|-----------|------|------|-----------------------|------|
|                           | a                                                            | b             | c             | d          | e         |      |      |                       |      |
| Blunt Post                | 1.08(27.4)                                                   | .162(4.1) dia | .050(1.3) dia | .590(15.0) | .115(2.9) | P9   | D1   | <b>901-9204-CC</b>    | 2    |
|                           | 1.08(27.4)                                                   | .162(4.1) dia | .050(1.3) dia | .590(15.0) | .115(2.9) | P13  | D1   | <b>901-9204-CCSF</b>  | 2    |
| Blunt Post                | 1.08(27.4)                                                   | .162(4.1) dia | .050(1.3) dia | .590(15.0) | .115(2.9) | P13  | D1   | <b>901-9757</b>       | 2    |
| Blunt Post                | .640(16.2)                                                   | .162(4.1) dia | .050(1.3) dia | .205(5.2)  | .060(1.5) | P13  | D1   | <b>901-9839</b>       | 2    |
| Blunt Post                | .562(14.3)                                                   | .162(4.1) dia | .050(1.3) dia | .087(2.2)  | .100(2.5) | P13  | D1   | <b>901-9184-CCSF</b>  | 2    |
| Blunt Post                | .560(14.2)                                                   | .162(4.1) dia | .050(1.3) dia | .060(1.5)  | .125(3.2) | P13  | D1   | <b>901-9789</b>       | 2    |
| Blunt Post, Solder Dipped | —                                                            | .085(2.2) dia | .010(0.3) dia | —          | —         | P13  | D1   | <b>901-9804-1</b>     | 3    |
| Tab ± .100 (2.5) Long     | Captive Contact, Flush TFE, Conforms to M83517/1-31004 (NQ)* |               |               |            |           | P12  | D1   | <b>901-9215-3CCSF</b> | 1    |