




Rotary Switches

105-SR2511F-17S, 105-SR2511F-19S, 105-SR2511F-25S,
105-SR2511F-26S, 105-SR2511F-26S, 105-SR2511F-33S,
105-SR2511F-34S, 105-SR2511F-42S, 105-SR2511F-43S,
105-SR2511F-62S, 105-SR2511F-12S

Dimensions: mm (in)



Electrical Specifications:

- Rating: 0.3A/125VAC
- Contact Resistance: 30mΩ max. @ 1A
- Insulation Resistance: 10MΩ @ 500VDC min.
- Dielectric Strength: 500VAC for 1 min.

Mechanical Specifications:

- Type: Shorting contact (make before break)
- Rotation Torque: 1~3KG/cm

Materials:

- Hardware Included: 1 hexagon nut & 2 washers
- Shaft: 1/4"

Note:

- RoHS Compliant

Mouser Stock No.	Poles	Position
105-SR2511F-17S	1	7
105-SR2511F-19S	1	9
105-SR2511F-25S	2	5
105-SR2511F-26S	2	6
105-SR2511F-33S	3	3
105-SR2511F-34S	3	4
105-SR2511F-42S	4	2
105-SR2511F-43S	4	3
105-SR2511F-62S	6	2
105-SR2511F-12S	1	12

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Alpha \(Taiwan\):](#)

[SR2511F-0403-26R0B-E9-S-W](#)