



FK32M

Long stem heavy duty T-handle penetration probe



Copyright © 2007 Test Products International, Inc.

Application

Heavy duty penetration into
semi-solids and liquids tapered
shaft resist bending

Range°F°C

-58° to 500°F
-50° to 250°C

Probe tip

22

Dimensions

Stem Length: 18" (457mm)
Diameter: 0.37"/0.15"
(9.5mm/3.76mm)
Lead Length: 39.4" (1M)

Insulation Material

Polyurethane