


SINGLE LEVEL RECTANGULAR LEDs



SERIES	CODE	COLOR	mA	Vf	Iv mcd
RP240	R	RED	10/30	2.0/2.8	2.0/4.0
RPT240	Y	YELLOW	10/30	2.1/2.8	1.5/3.0
RPV240	G	GREEN	10/30	2.1/2.8	1.5/3.0
	B	BLUE	30/50	3.2/3.7	0.5/0.8
RP280	R	RED	10/30	2.0/2.8	1.5/3.8
RPT280	Y	YELLOW	10/30	2.1/2.8	1.5/3.0
RPV280	G	GREEN	10/30	2.1/2.8	1.5/3.0
	B	BLUE	30/50	3.2/3.7	0.4/0.6

SERIES	CODE	COLOR	mA	Vf	Iv mcd
RP210	R	RED	10/30	2.0/2.8	1.0/2.0
RPT210	Y	YELLOW	10/30	2.1/2.8	1.0/2.0
RPV210	G	GREEN	10/30	2.1/2.8	2.5/4.5
SP200	R	RED	10/30	2.0/2.8	0.3/1.0
SPT200	Y	YELLOW	10/30	2.1/2.8	0.4/1.5
SPV200	G	GREEN	10/30	2.1/2.8	0.4/1.3


- ALL "Vf" READINGS ARE TYP/MAX
- ALL "mcd" READINGS ARE MIN/TYP

SAMPLE PART NUMBER:

RP280X3

LED COLOR

BILEVEL RECTANGULAR LEDs



SAMPLE PART NUMBER:
21RPV070T3-X/X

LED 2 COLOR
LED 1 COLOR

Arrays

CODE	COLOR	mA	Vf	Iv mcd
R	RED	10/30	2.0/2.8	1.2/3.0
Y	YELLOW	10/30	2.1/2.8	1.0/2.3
G	GREEN	10/30	2.1/2.8	1.2/3.0
B	BLUE	30/35	3.2/3.7	0.6/1.1

SPECIALS

- ALL "Vf" READINGS ARE TYP/MAX
- ALL "mcd" READINGS ARE MIN/TYP
- LC = LOW CURRENT 2mA LEDs
- X = DENOTES BLANK LED SPACE
- CONSULT FACTORY ON PART NUMBERS FOR ARRAYS WITH NONCONSECUTIVE COLORS

