



Datasheet for part number 121073-3981 D

|                                                                              |
|------------------------------------------------------------------------------|
| Our Catalog Part Number: DE-9S-1-A-8-N-A191-A197                             |
| Our Global Manufacturing Part Number: 121073-3981 D                          |
| Brand: Cannon Product Category: D Sub Product Line: D Sub Series: ORIGINAL D |

| Product Datasheet               |                                                           |
|---------------------------------|-----------------------------------------------------------|
| General                         | Standard D-Subminiature                                   |
| Wire Gauge Range AWG            | AWG 20-28                                                 |
| Mating Cycles                   | 200                                                       |
| Dielectric Withstanding Voltage | 1200 VAC at sea level                                     |
| Current Rating                  | 7.5 A at 85°C / 5 A at 105°C                              |
| Contact Resistance              | 10 milli Ohm max                                          |
| Operating Temperature           | -55°/+125°                                                |
| Salt Spray Test                 | 20 hours                                                  |
| Shell Material                  | steel                                                     |
| Shell Finish                    | tin                                                       |
| Insulator Material              | Thermoplastic, type PCT UL 94V-0                          |
| Insulator Color                 | black                                                     |
| Contact Arrangement             | 9 contacts size 20                                        |
| Gender                          | Socket                                                    |
| Contact Type                    | turned                                                    |
| Contact Material                | copper alloy                                              |
| Contact Finish                  | gold over nickel (Performance Class 2)                    |
| Contact Termination             | Right angled solder                                       |
| Termination Direction           | contact termination at short side of trapezoid (Standard) |
| Mounting Methode                | Metal bracket with 4-40 Screwlock                         |