



UNIT:mm



Electronic Test:
1.100% Test,(Open,Short,Miss Wire)
2.Contact Resistance:3 ohm max.
3.Insulation Resistance:5M ohm min.
4.Hi-Pot:300V DC/10ms



1PCS/PE BAG

⑩	TUBE	2	HEAT SHRINK TUBE BLACK OD1.5*1=15MM
⑨	PE BAG	1/10	CLEAR SIZE:280*330*0.05mm PRINT BLACK"MADE IN CHINA"+10PCS"
⑧	TIE	1	WHITE L=120mm
⑦	PE BAG	1	CLEAR SIZE:130*230*0.05mm PRINT BLACK"MADE IN CHINA"+1"PC"
⑥	COPPER FOL	2	DOUBLE-SIDED CONDUCTIVE COPPER FOL 180" W25mm*1.55mm
⑤	SCREW	4	SCREW#4-40UNC L47mm,NICKEL PLATED,INSULATION COLOR BEIGE(V-29)
④	OUT JACKET	43.5g	BEIGE(V-29) 40P PVC(MOULD NO:MM-113)
③	IN JACKET	8g	CLEAR LDPE(MOULD NO:MM-049)
②	CONN	1	HD15P FEMALE,PIN G/F,SHELL-NICKEL,INSULATION COLOR:BLUE. SOLDER TYPE.
①	CABLE	1	NOUL 28AWG(7/0.12T0)*14C+AL/MR+D.W(7/0.12 TC) OUTER JACKET COROL:BEIGE(V-29) OD:6.0±0.15mm. L=2000±20mm.

SPECIFICATION

PIN ASSIGNMENT			
P1	1	white	P2
	2	grey	1
	3	yellow	2
	4	pink	3
	5	orange	4
	6	red	5
	7	brown	6
	8	green	7
	10	blue	8
	11	purple	10
	12	light green	11
	13	light blue	12
	14	black	13
	15	white/black	14
Shell		drain	15
			Shell

Cnc Tech, LLC
Industrial Cable and Connector Technology

DRAWN BY	ZHONGHS	DRAWING NO.	
CHECKED BY		CUSTOMER	
APPROVAL BY		ITEM NO.	731-10061-00200
DECIDE BY		DATE	2012-02-15
VERSIONS/EDITED	A/0	PROJECTION	