

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0945360101

Status:

Active

Overview:

Standard Quick-Disconnect Terminals

Description:

Quick Disconnect, Flag Terminal for (1.50-0.50mm²) 16-24 AWG Wire, Accepts 4.75 x 0.81mm Tab, Post-Tin Plated

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Quick Disconnects
Series	94536
Crimp Quality Equipment	Yes
Insulated	No
Overview	Standard Quick-Disconnect Terminals
Product Name	N/A
Type	Quick Disconnect
UPC	822348698356
Physical	
Barrel Type	Open
Gender	Female
Glow-Wire Compliant	No
Insulation	None
Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.492/g
Orientation	Flag
Packaging Type	Reel
Polarized to Mating Part	Yes
Tab Thickness	0.81mm
Tab Width	5.60mm
Temperature Range - Operating	-40°C to +80°C
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.00mm max.
Wire Size AWG	16, 18, 20, 22, 24
Wire Size mm²	0.50-1.50
Electrical	
Voltage - Maximum	250V
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-94536-002

EU ELV

Compliant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -ED/01/2017 (12 January 2017)

Halogen-Free

Status

Not Relevant

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Relevant

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

94536 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION