





ISO 5745, DIN ISO 5745, NF E 73-102

- Side cutter for steel wire up to 160 kg/mm².
- Serrated jaws with central area for handling rods.
- Strong rigid jaws for positive grip.
- 4 options :
 - CPE : Chrome finish, ergonomic grips, return spring.
 - TE : Varnish finish, ergonomic grips, return spring.
 - G : Varnish finish, PVC grips.
 - VE : Varnish finish, return spring, 1000V insulated grips for electrical safety to EN 60900 and , for working on or near live components.



	 max mm Cu-Fe	D x E mm	L mm	A mm	B mm	C mm	 g
193.16CPE	3 - 1,6	2,9 x 3,6	168	46	18	9	130
185.20CPE	3,5 - 1,6	3,2 x 4,9	200	75	18	9	200
185.20TE	3,5 - 1,6	3,2 x 4,9	200	75	18	9	200
193.16G	3 - 1,6	2,9 x 3,6	160	46	18	9	115
185.20G	3,5 - 1,6	3,2 x 4,9	196	75	18	9	165
193.16VE	3 - 1,6	2,9 x 3,6	168	46	18	9	130
185.20VE	3,5 - 1,6	3,2 x 4,9	200	75	18	9	200