

24V Flexiprint

high bright (PLCC6)

Specifications

Voltage	24V
Current	3A
Wattage	14.4W/m
Number of LED's	300pcs
Length of Stripe	5meter
Operating Temperature	-25°~+60°C
Storage Temperature	-40°~+80°C

Benefits


Adhesive tape on backside
RoHS compliant



Electrical and Optical Characteristics (Ta=25°C)

Part Number	Colour	Wavelength	Intensity lm
FP3-B02D-500	 blue	470 nm	1200
FP3-G02D-500	 green	520 nm	2700
FP3-N02D-500	 warmwhite	3000-3500 °K	2500-2800
FP3-R02D-500	 red	621 nm	1200
FP3-S02D-500	 naturalwhite	4000-5000 °K	2600-3000
FP3-W02D-500	 white	6500-7500 °K	2700-3200
FP3-Y02D-500	 yellow	590 nm	1500

Dimensions



Thickness: 2.1 mm

1. All specifications according to information from our manufacturers, without additional guarantee on our part
2. All dimensions are in millimetres
3. Tolerance is ± 0.2 mm unless otherwise specified
4. Specifications are subject to change without notice