



General ordering data

Order No.	1736960000
Part designation	SKMU M40 K SW
Version	Locknut, Polyamide 6, External thread: M 40 x 1.5
EAN	4008190956431
Qty.	10 pc(s).

General details

AF size 1	50 mm
Assembly temperature, max.	100 °C
Assembly temperature, min.	-30 °C
External thread	M 40 x 1.5
Internal thread	M 40 x 1.5
Length of thread	7 mm
Material	Polyamide 6
RAL colour	RAL 9005
Thickness	7 mm
Type of cable gland	metric

Approvals

Approvals institutes	n.a.
----------------------	------

Classifications

ETIM 2.0	EC000940
ETIM 3.0	EC000940
eClass 4.1	23-11-07-01
eClass 5.0	23-11-07-01
eClass 5.1	23-11-07-01

Similar products

Order No.	Part designation	Version
1736920000	SKMU M16 K SW	Locknut, Polyamide 6, External thread: M 16 x 1.5

1736930000	SKMU M20 K SW	Locknut, Polyamide 6, External thread: M 20 x 1.5
1736940000	SKMU M25 K SW	Locknut, Polyamide 6, External thread: M 25 x 1.5
1736950000	SKMU M32 K SW	Locknut, Polyamide 6, External thread: M 32 x 1.5
1736970000	SKMU M50 K SW	Locknut, Polyamide 6, External thread: M 50 x 1.5
1736980000	SKMU M63 K SW	Locknut, Polyamide 6, External thread: M 63 x 1.5
1719120000	SKMU PG11-K SW	Locknut, Polyamide 6, External thread: PG 11
1719130000	SKMU PG13,5-K SW	Locknut, Polyamide 6, External thread: PG 13.5
1719140000	SKMU PG16-K SW	Locknut, Polyamide 6, External thread: PG 16
1719150000	SKMU PG21-K SW	Locknut, Polyamide 6, External thread: PG 21
1719160000	SKMU PG29-K SW	Locknut, Polyamide 6, External thread: PG 29
1719170000	SKMU PG36-K SW	Locknut, Polyamide 6, External thread: PG 36
1719180000	SKMU PG42-K SW	Locknut, Polyamide 6, External thread: PG 42
1719190000	SKMU PG48-K SW	Locknut, Polyamide 6, External thread: PG 48
1719100000	SKMU PG7-K SW	Locknut, Polyamide 6, External thread: PG 7
1719110000	SKMU PG9-K SW	Locknut, Polyamide 6, External thread: PG 9