



Date	SYM	REVISION RECORD	AUTH	DR.	CK.
09/26/14	B	REDRAWN IN AUTOCAD UPDATED TO ROHS 2 COMPLIANT	T.B.	B.S.	



NOTES:

SPECIFICATION:

1. MATERIAL:

HOUSING : BLACK POLYPROPYLENE

FLAMMABILITY RATING -UL94-HB, UL FILE NO. E216959

TEMPERATURE RANGE: -10°C to +100°C

RIVETS: BRASS, NICKEL PLTD.

WIRES: 26 AWG, UL1007, CSA-TR-64, 300V, 80°C

SPRING: SPRING STEEL, NICKEL PLTD.

CONTACT RESISTANCE: UNDER 50mΩ FOR +/- CONTACTS PER
EIA-540J000

ROHS 2 COMPLIANT

MOUNTING INSTRUCTION:

USE 2-56 MACHINE SCREWS OR EYELETS 0.089" OD
BY 0.15" FLANGE STIMPSON GS-3 SERIES OR EQUIVALENT.
ALSO ADHESIVES AND DOUBLE SIDED TAPES WORK WELL.

Tolerance (Except as noted)	 Memory Protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735		
decimal ±.5 (.020)			Scale Drawn By B.S. Approved By T.B.
Fractional ± .8 (.030)	Title 4 "D" CELL HOLDER WITH WIRE LEADS		
Angular ± 3°	Date 9/26/14	Drawing Number BH14DW	