

PICCOLO PC F 85 G



Sample photo

Order symbol: PC F 85 G
Product nbr: 8724312
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074002211
El. number:
Finland: 3423415
Denmark: 8212001637
Italy: 7201045
Sweden: 2536823
Norway: 2536515

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:			Length	Width	Height	Rating:
mm:	230	80	85			Ingress Protection (EN 60529): IP 66/67
inch:	9.1	3.1	3.3			Impact Resistance (EN 62262): IK 08
Materials:						Electrical insulation: Totally insulated
Material:	Polycarbonate					Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:	RAL 7035					UV resistance: UL 508
Cover colour:	RAL 7035					Flammability Rating (UL 746 C 5): UL 746C 5V
Cover screws material:	Polyamide					Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws colour:	Grey					NEMA Class: NEMA 1, 4X, 6, 6P, 12, 13
Gasket material:	Polyurethane					
Temperatures:						Certificates:
Short term:	-40 ... 120 °C					Germanischer Lloyd (GL)
Continuous:	-40 ... 80 °C					Underwriters Laboratories
Short term:	-40 ... 250 °F					Fimko
Continuous:	-40 ... 175 °F					Europe EN 62208: 2003
						UL Canada
						Gost R
Accessories:						
F-MP	Mounting plate					
FM-3	DIN-35 Mounting rail					
FP 22040	Wall fastening lug (2 pcs)					

PICCOLO 230x80x65-85

