

Combination Photo Tachometer/Stroboscope

✓ **2 meters in one - Stroboscope to analyze rotating objects**
Plus a Non-Contact Tachometer to measure rpms

Features:

- Unique display where characters reverse direction depending on measurement mode you are in
- Large 0.4" 5 digit LCD digital display
- Microprocessor based with quartz crystal oscillator to maintain high accuracy
- Tachometer memory stores last, max and min readings
- Performs Tachometer RPM measurement and Stroboscopic speed and motion analysis
- Stroboscope course and fine flash rate adjustments in three ranges
- Battery operation brings motion analysis to any location
- Complete with four 1.5 volt AA batteries, reflective tape and carrying case



Specifications	Photo	Strobe
Range RPM	0.5 to 20,000	5 to 99,999
Accuracy		±(0.1% +2digits)
Surface Speed	0.2 to 6560 ft/min	
Sampling Time	1sec > 6 RPM	1 Sec ≥ 60 RPM
Resolution	0.1 RPM (<1,000 RPM) 1 RPM (≥ 1,000 RPM)	0.1 FPM (<1,000 FPM) 1 FPM (≥1,000 FPM)
Power	4 x 1.5V AA Batteries	
Dimensions	8.5 x 2.6 x 1.5" (215 x 65 x 38mm)	
Weight	10.6oz (300g)	

Ordering Information:

461825Combination Tachometer/Stroboscope
461825-NIST461825 with NIST certificate
461937Spare Reflective Tape (23" each strip),10pk



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Extech:](#)

[461825](#) [461825-NIST](#)