









Telecommunication ADSL Transformer Transformers

DT32-2019BT
DT32-2020BT
DT32-2021AT
DT32-2062AT

• DT32-20XXXX
DELTAXXXX



XXXX : DATE CODE
WHITE DOT ON PIN1



DIMENSIONS IN mm

A	B	C	D	E	F	G
12.7 MAX.	2.79 MIN.	14.0 MAX.	14.0 MAX.	10.16 ±0.3	2.54 ±0.3	

ELECTRICAL CHARACTERISTICS

	DT32-2019BT	DT32-2020BT	DT32-2021AT	DT32-2062AT
T.R	(PRI:SEC): 1.2:1 ± 2% @20KHz 1V	(PRI:SEC): 1:1.8 ± 2% @10KHz 0.1V	(PRI:SEC): 1:1.8 ± 2% @10KHz 0.1V	(PRI:SEC): 1.2:1 ± 1% @10KHz 0.1V
L	PRI: 3.96mH ± 5% @10KHz 0.1V	PRI: 3.96mH ± 5% @10KHz 0.1V	PRI: 3.96mH ± 5% @10KHz 0.1V	PRI: 3.96mH ± 5% @10KHz 0.1V
L.K	PRI: 15uH Max. @100KHz 0.1V	PRI: 18uH Max. @100KHz 0.1V	SEC: 20uH Max. @100KHz 0.1V	PRI: 18uH Max. @100KHz 0.1V
D.C.R	N1: 1.91Ω ± 10% N2: 1.91Ω ± 10% SEC: 4.0Ω ± 10%	N1: 2.04Ω ± 10% N2: 2.04Ω ± 10% SEC: 7.40Ω ± 10%	N1: 2.20Ω ± 10% N2: 2.20Ω ± 10% N3: 4.55Ω ± 10% N4: 4.80Ω ± 10%	N1: 2.40Ω ± 10% N2: 2.40Ω ± 10% N3: 2.25Ω ± 10% N4: 1.80Ω ± 10%
HI-POT	1500 VAC 2 SEC	1500 VAC 2 SEC	1500 VAC 2 SEC	1500 VAC 2 SEC
C	40pF Max. @10KHz 1V	40pF Max. @10KHz 1V	-----	-----
I.L	-----	-----	1.0 dB Max. @772KHz	-----
L.B	40dB Min. @20KHz~1.1MHz	40dB Min. @20KHz~1MHz	38dB Min. @20KHz~1.1MHz	40dB Min. @20KHz~1.1MHz
FR	-----	-----	-----	-----
R.L	-----	-----	-----	-----
T.H.D	-----	-----	-----	-----
Schematic	3	3	1	1

DELTA ELECTRONICS, INC.

(TAOYUAN PLANT CPBG) 31-1, SHIEN PAN ROAD, KUEI SAN INDUSTRIAL ZONE, TAOYUAN SHIEN, TAIWAN, R.O.C.
TEL: 886-3-3626301 FAX: 886-3-3618901
<http://www.deltaww.com>