




ALL TOLERANCES = ±0.004 [±0.10]
UNLESS OTHERWISE INDICATED

BACK SHELL KIT INCLUDES:

- 2 - BACK SHELL HALVES
- 2 - 4-40 MATING SCREWS
- 2 - SADDLE WASHERS
- 2 - HOUSING SCREWS
- 2 - HOUSING NUTS
- 1 - GROMMET TREE - VARIOUS SIZES
(NON-CONDUCTIVE GROMMETS)


MATERIAL: DIE-CAST ZINC ALLOY
PLATING: NICKEL
OPERATING
TEMPERATURE: -45°C TO +120°C




DO NOT SCALE FROM DRAWING

RoHS COMPLIANT


	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: C. SMITH		DATE: 04-20-10	
		CHECKED:		DATE:	
			SCALE: 1 : 1	SHEET 1 OF 2	REV 3
			DWG NO. 979-009-030R121		




MATING SCREW



HOUSING SCREW




SADDLE WASHER



HOUSING NUT

ALL HARDWARE:
MATERIAL = BRASS
PLATING = NICKEL
TOLERANCE = ±0.002 [±0.05]
SCALE = 2 : 1

RoHS COMPLIANT



DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: C. SMITH		DATE: 04-20-10		
		CHECKED:		DATE:		
NorComp			SCALE: AS SHOWN		SHEET 2 OF 2	REV 3
			DWG NO. 979-009-030R121			