


JFETs (Cont'd)




TO-71

Description	I _{oss} Min. (mA)	Max. Off-Set (mV)	Part Number
Dual Low-Noise Amplifier	0.5	5	U401
Dual Low-Noise Amplifier	0.5	10	U402
Dual Low-Noise Amplifier	0.5	10	U403
Dual Low-Noise Amplifier	0.5	15	U404
Dual Low-Noise Amplifier	0.5	20	U405
Dual Low-Noise Amplifier	0.5	40	U406
Dual High-Gain Amplifier	5	5	2N5564
Dual High-Gain Amplifier	5	1	2N5565
Dual High-Gain Amplifier	5	20	2N5566
Dual High-Frequency Amplifier	6	10	U440
Dual High-Frequency Amplifier	6	20	U441

Description	Max. Reverse Current (pA)	Part Number
Low-Leakage Diode	-5	DPAD5
Low-Leakage Diode	-50	DPAD50

Description	I _{oss} Min. (mA)	Max. (mV) Off-Set	Part Number
Dual Amplifier	0.7	5	2N5196
Dual Amplifier	0.7	5	2N5197
Dual Amplifier	0.7	10	2N5198
Dual Amplifier	0.7	15	2N5199



TO-78

Description	Max. Offset (mV)	Part Number
Dual Low-Leakage JFET	10	U421
Dual Low-Leakage JFET	15	U422
Dual Low-Leakage JFET	25	U423

Description	Max. Reverse Current (pA)	Part Number
Low Leakage Diode	-1	DPAD1

Description	Max. Offset (mV)	Part Number
Dual High-Frequency Amplifier	10	2N5911
Dual High-Frequency Amplifier	15	2N5912
Dual High-Frequency, Low-Noise Amplifier	-	U430
Dual High-Frequency, Low-Noise Amplifier	-	U431