






THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 19
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS
RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS					DATE	APPROVED
P	F	ZONE	LTR	DESCRIPTION		
		A		REV PER EC 0730-3607-91	1-6-94	RV RS


1. WIRE RANGE : 24-18 AWG.
INSULATION RANGE : .130 DIA. MAX.



SECTION A-A



SECTION B-B

DETAIL A
SCALE 20:1

770211-1 SHOWN

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS .015 ANGLES .015		CONTRACT NO. DR 12-11-85 CHK 12-11-85 APPD 12-11-85 DSGN APPD OTHER APPD		PART NO.	
MATERIAL .012 BRASS		FINISH PRE-TIN		NAME AMP AMP INCORPORATED Harrisburg, Pa. 17105	
SIZE D		FSCM NO. 00779		DRAWING NO. 770211	
SCALE 10:1		SHEET			

CUSTOMER DRAWING