


Glassockellampen

T15

Socket W2,1x9,5d

(15 x 36 mm)


Spannung	Strom	Leistung	Artikel-Nr.	EAN 4021553...	Preis/St. in €
12V	400mA	5W	00575126	375250	2,05
	600mA	7W	00575127	375267	2,70
	670mA	8W	00575129	375342	2,70
	830mA	10W	00575121	375274	2,70
	1,25A	15W	00575122	375281	2,25
	1,66A	20W	00575123	375298	2,25
24V	210mA	5W	00575245	375304	2,70
	420mA	10W	00575241	375311	2,70
	625mA	15W	00575242	375328	2,70
	875mA	21W	00575243	375335	2,70



Rigid-Loop Xenon-Lampe

(10 x 44 mm)

Spannung	Leistung	Ausführung	Artikel	EAN 4021553...	Preis/St. in €
12V	5W	klar	10701205	614564	3,80
	5W	matt	10711205	614571	4,05
	8,5W	klar	10701285	614588	3,80
	8,5W	matt	10711285	614595	4,05
	10W	klar	10701210	614601	3,80
	10W	matt	10711210	614618	4,05
24V	5W	klar	10702405	614625	3,80
	5W	matt	10712405	614632	4,05
	8,5W	klar	10702485	614663	3,80
	8,5W	matt	10712485	614670	4,05
	10W	klar	10702410	614687	3,80
	10W	matt	10712410	614694	4,45
26V	8,5W	klar	10702685	614700	5,10
	8,5W	matt	10712685	614717	a.Anfrage



Kleinlampen