






Front View

Pin Block



Rear View

Materials and Finish

Insulator: PBT thermoplastic,
UL94V-0 rated, black color

Contact Material: bronze, gold flash
plated

Metal Sleeve: brass, 0.40 thick,
nickel plated

Electrical Characteristics

Insulation Resistance:
50 Megohms min. at 250V DC



Dielectric Withstanding Voltage:
250V AC rms, 60Hz for 1 minute

Contact Resistance:
30 milliohms max.

Current Rating:
12V DC at 2A max.
100V AC at 1A max.


Operating Temperature:
-40°C to +85°C

Metal Sleeve



Tolerances	
X.X ± 0.25	
X.XX ± 0.15	
Unless Stated	
Otherwise	

REV.	DATE	DESCRIPTION	REV. BY	CHK. BY	DRAWN BY	DATE
A0	3/10/03	New Drawing	C. Leiva	T. Gokcek	C. Leiva	3/10/03
A1	3/28/03	Release Drawing	T. Gokcek	C. Leiva		
A2	11/4/04	ECO #04-062	C. Leiva	C. Furumasa		
A3	12/20/04	ECO #04-071	R. Aguirre	H. MA		



UNITS
mm

KMDM-GEO-9P

Mini-DIN Plug Kit

9 pos. GeoPort type, gold flash plating



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[KMDM-GEO-9P](#)