



Sample photo

Order symbol: CAB ABS 403018 G3B
Product nbr: 8183352

Description: Cabinet, ABS
Remarks: Locks on the long side

EAN: 6418074020307
El. number:
Finland 3424318
Denmark 8212019043
Italy 7811045
Sweden 2540075

Including: Cabinet base, door with EPDM gasket, 3mm double bit lock(s) with key, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:	L	W	H
mm:	400	300	180
inch:	15.7	11.8	7.1

Materials:	
Material:	ABS
Base colour:	RAL 7035
Cover colour:	RAL 7035
Gasket material:	EPDM

Temperatures:	
Short term:	-40 ... 80 °C
Continuous:	-40 ... 60 °C
Short term:	-40 ... 175 °F
Continuous:	-40 ... 140 °F

Accessories:	
EKIV 43	Mounting plate
EKIV 27	DIN-35 Mounting rail
EKIV 37	DIN-35 Mounting rail
FP A 43	Swing-out door, aluminium
FP 43	Front plate
FP 12x2-43	Front Plate
FP 12x3-43	Front Plate
DRF 43/44	DIN rail frame set

Rating:	
Ingress Protection (EN 60529):	IP 65
Impact Resistance (EN 50102):	IK 08
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	Yes
Flammability Rating (UL 746 C 5):	UL 94 HB
Glow Wire Test (IEC 695-2-1) °C:	650
NEMA Class:	NEMA 1, 4, 4X, 12, 13

Certificates:	
Fimko	
Europe EN 50298 1998	
Gost R	

