




HONEYWELL
PART NUMBER
SEE CHART

REV	DOCUMENT	CHANGED BY	CHECK
B	0055056	SSK 27JUL09	CMH

.090 APPROX. PULLOUT
TO CHANGE POSITION

"A" LOCKED IN THREE POSITIONS	"B" LOCKED IN CENTER AND EXTREME POSITION (KEYWAY SIDE)	"D" LOCKED OUT OF CENTER POSITION	"E" LOCKED IN CENTER POSITION	"F" LOCKED IN EXTREME POSITION (OPPOSITE KEYWAY)	 LOCKWASHER (PART NO. TS-10013)
"G" LOCKED IN EXTREME POSITION (KEYWAY SIDE)	"H" LOCKED OUT OF CENTER AND EXTREME POSITION (KEYWAY SIDE)	"J" LOCKED OUT OF CENTER AND EXTREME POSITION (OPPOSITE KEYWAY)	"K" LOCKED IN CENTER AND EXTREME POSITION (OPPOSITE KEYWAY)	"L" LOCKED OUT OF EXTREME POSITION (KEYWAY SIDE)	 LOCKING RING (PART NO. EN-12449)
"M" LOCKED OUT OF AND INTO EXTREME POSITION (OPPOSITE KEYWAY)	"N" LOCKED OUT OF EXTREME POSITION (OPPOSITE KEYWAY)	"P" LOCKED OUT OF AND INTO EXTREME POSITION (KEYWAY SIDE)			
CAT. LIST. 	RECOMMENDED LOCKING COMBINATIONS FOR CONFIGURATION SEE LETTERED DETAILS	CIRCUIT WITH TOGGLE IN			 HEX NUT (2) (PART NO. TL-10632)
		EXTREME POSITION KEYWAY SIDE (1-2)	CENTER	EXTREME POSITION OPPOSITE KEYWAY (2-3)	
11TW59-1	A, B, D, E, F, G, H, J, K, L, M, N, P	ON	OFF	ON	
11TW59-3	D, F, G	ON	NONE	ON	

NOTES

- 1 FURNISHED UNASSEMBLED
2 SUFFIX MUST BE ADDED FOR DESIRED TYPE TOGGLE LOCKING
3 - TERMINALS ARE PLATED FOR SOLDERING
4 MATTE FINISH

ELECTRICAL DATA	DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACES X ± .400 ONE PLACE .X ± .03 TWO PLACE .XX ± .015 THREE PLACE .XXX ± .005 ANGLES X ± 3.0° THIRD ANGLE PROJECTION 	DRAWN	KRB	13 OCT07	Honeywell					
		CHECK	MJS	13 OCT07						
CODE L117 5A - 125 VAC 		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE					
		INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SWITCH, TOGGLE					
		RASTER			SIZE	TYPE	CAGE CODE	DRAWING NAME		REV
					C	I	-	11TW59 SERIES CHART 2		B
					SCALE		NTS		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[11TW59-3D](#) [11TW59-1A](#)