

Nut - A-INL-M20-P-BK - 1411215

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Nut, Cable gland material: Polyamide 6, PA 6 GF 30, For threads M20, Color: jet black



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	5 pc
Weight per Piece (excluding packing)	4.0 g
Custom tariff number	39269097
Country of origin	Turkey

Technical data

Dimensions

Length	6 mm
Connecting thread diameter	20 mm
Wrench size, counter nut	26 mm
Hexagon angular dimension GRP	28.6 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 100 °C
---------------------------------	-------------------

General

Material	PA 6 GF 30
Cable gland material	Polyamide 6
Flammability rating according to UL 94	V2
Color	jet black RAL 9005
	jet black

Standards and Regulations

Nut - A-INL-M20-P-BK - 1411215

Technical data

Standards and Regulations

Flammability rating according to UL 94	V2
--	----

Classifications

eCl@ss

eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 8.0	23110701

ETIM

ETIM 4.0	EC000032
ETIM 5.0	EC000129

Drawings

Dimensional drawing

