



## FEMALE FACE VIEW



## MALE FACE VIEW



883031A09M010

no poles      cable typ  
3-5 pole      #22/3-5

cable length  
010----1 Meter  
100----10 Meters

## CONNECTOR SPECIFICATION:

VOLTAGE RATING	250 VAC/VDC
AMPERAGE RATING	max. 4 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-20°C TO 105°C
UL CERTIFICATIONS	UL RECOGNIZED, FILE NO. E152210
ASSEMBLY IS	RoHS COMPLIANT

COMPONENT	MATERIAL	FINISH
LABEL	MYLAR	BLACK/YELLOW
COUPLER	BRASS	NICKEL PLATED
PIN CONTACT	COPPER ALLOY	GOLD OVER NICKEL
INSERT	NYLON	BLACK
OVERMOLD	PUR	YELLOW
CABLE- 22/3-5 (COPPER STRANDING) 3/4/5 CONDUCT. 300V	JACKET: PVC	JACKET: YELLOW

MATERIAL NUMBER	ENGINEERING NUMBER	FINISHED LENGTH
1200661137	883031A09M010	1.0M +55.6 -0 [3.28' +2.19" -0]
1200661389	885031A09M010	1.0M +55.6 -0 [3.28' +2.19" -0]
1200661262	884031A09M010	1.0M +55.6 -0 [3.28' +2.19" -0]
1200661280	884031A09M100	10.0M +55.6 -0 [32.8' +2.19" -0]

UPDATED FOR PART MATRIX		QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE NTS	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	
EC NO.:IPG2014-0988	11/26/13		mm	INCH	DRAWN BY LSTEMMML	DATE 2010/01/25				
DRWN:GUUSTAFS	CH'KD:TWOLDEGE	 = 0	4 PLACES	±---	±---	CHECKED BY RE	DATE 2010/01/26	MICRO-CHANGE CORDSET 3/4/5 POLE FE 90 /MA STR 22/AWG YELLOW PVC CABLE		
APPR:BWODMAN	2010/01/29		3 PLACES	±---	±.005					
			2 PLACES	±.13	±.010					
			1 PLACE	±.25	±.020	APPROVED BY NSTAUDIG	DATE 2010/01/29			
			ANGULAR ± .5 °							
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE CHART		DOCUMENT NO.	MOLEX INCORPORATED		
A	REV:			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					