




YEQ-110-01-L-5



YEQ-116-01-F-Q



YTS-114-01-F-6

(2.00 mm) .0787"

YTS, YEQ SERIES

HIGH-DENSITY SOCKET STRIP

SPECIFICATIONS

For complete specifications see www.samtec.com?YTS or www.samtec.com?YEQ

Insulator Material:

Black Liquid Crystal Polymer

Contact Material:

Phosphor Bronze

Operating Temp Range:

-55 °C to +125 °C

Plating:

Sn or Au over 50 μ" (1.27 μm) Ni

Insertion Depth:

(2.62 mm) .103" to (5.03 mm) .198"

Max Cycles:

100 with 10 μ" (0.25 μm) Au

RoHS Compliant:

Yes

Mates with:

YTT, YTW, YTE, TMMS



Choice of four, five or six row

(2.00 mm) .0787" pitch

(6.35 mm) .250"

(2.00 mm) .0787" TYP

PROCESSING

YTS Lead-Free Solderable:

Wave Only

YEQ Lead-Free Solderable:


Wave or reflow with Matte Sn plating

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



FILE NO. E111594



Note:
Some lengths, styles and options are non-standard, non-returnable.