

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19154-0037

Status:

Active

Overview:

Splices

Description:

InsulKrimp™ Butt Splice for 10-12 AWG Wire



Series

image - Reference only

Documents:

- Drawing (PDF)

Product Specification PS-19902-013 (PDF)
- Product Specification PS-19902-007 (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification PS-19902-011 (PDF)

Agency Certification

CSA

LR18689

UL

E32244

General

Product Family

Splices

Series

19154

Crimp Quality Equipment

Yes

Mil-Spec

N/A

Overview

Splices

Product Name

Butt, InsulKrimp™

UPC

800753109025

Physical

Barrel Type

Closed

Color - Resin

Yellow

Flammability

94V-0

Insulation

PVC

Material - Metal

Copper

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

PVC

Net Weight

3.084/g

Packaging Type

Bag

Wire Size AWG

10, 12

Material Info

Old Part Number

CS-V-346X

Reference - Drawing Numbers

Product Specification

PS-19902-007, PS-19902-011, PS-19902-013

Sales Drawing

6000208C

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19154Series

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050300
PremiumGrade™ Hand Crimp Tool	0640010100
Hand Crimp Tool	0640010300
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050100

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19154-0037](#)